


LEFT SURFACE			MATERIAL		RIGHT SURFACE		
R 17,421 CX Øe 24 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -			GLASS Fused Silica 458/678 Nd: 1,458		R ∞ PL Øe 24 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 2,18' 5/ 40 - 20 6/ -		
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110			FIRST ANGLE PROJECTION  ALL DIMS IN: mm		 Edmund Optics® TITLE 25mm Dia x 38mm FL, 785NM V-COAT Coated, Plano-Convex Lens DWG NO 25913 SHEET T SIZE A4 SHEET 1 OF 1		