





FOCAL LENGTH (EFL): 100 ±1
 BACK FOCAL LENGTH (BFL): 98,7

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	91,094±0,091 CX	GLASS FUSED SILICA 458/678	R	91,094±0,091 CX
Øe	24		Øe	24
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE 25mm Dia, x 100mm FL, Uncoated, UV Double-Convex Lens				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN:	mm			DWG NO 48297	SHEET SIZE A4	SHEET 1 OF 1
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING									
INDICATIONS IN ACCORDANCE WITH ISO 10110									