




NOTES:

1. COATING (APPLY ACROSS CLEAR APERTURE)
 LASER V-COAT
 R(abs) 0.25% @ 532 nm

2. RoHS COMPLIANT



**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

DAMAGE THRESHOLD, BY DESIGN	7.5 J/cm ² @ 20ns , 20 Hz @ 355 nm
DESIGNED WAVELENGTH DWL (nm)	355
TRANSMISSION	> 97.5 @ DWL
TRANSMITTED WAVEFRONT, P-V	< $\lambda/4$ for Input Beam 3mm (2X-6X) < $\lambda/4$ for Input Beam 2.5mm (2X-8X)



ALL DIMS IN

mm

EO[®] Edmund Optics[®]

TITLE

355nm 2X - 8X Gemma[®] Variable Beam Expander

DWG NO

15546

SHEET
 1 OF 1