


NOTES:

1. SUBSTRATE : Germanium (Ge)
2. COATING (APPLY ACROSS CLEAR APERTURE)
 S1: UNCOATED
 S2: UNCOATED


3. FINE GRIND SURFACE



**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
CLEAR APERTURE	85%	85%
ANGLE TOL. (arcmin)	±10	±10
SURFACE QUALITY	60-40	60-40
SURFACE FLATNESS	2λ	2λ
WAVELENGTH RANGE (nm)	2000 - 14000	2000 - 14000
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE: Germanium, 12.7mm, Uncoated, ISP Optics IR Right Angle Prism

DWG NO: 25040

SHEET 1 OF 1