


NOTES:

1. SUBSTRATE:  
Silicon (Si)
2. CENTERING TOLERANCE:  
EDGE THICKNESS VARIATION: <20µm
3. COATING (APPLY ACROSS CLEAR APERTURE)  
  
S1&S2: NONE

4. FINE GRIND SURFACE

5. SURFACE ROUGHNESS: <100 Ra



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	CONVEX	CONCAVE
RADIUS	44.82	67.12
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	ø22.86	ø22.86
IRREGULARITY AT 632.8nm	λ/4	λ/4
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN

mm

**EO**® Edmund Optics®

TITLE

25.4mm Dia. x 50.8mm FL, Uncoated, ISP  
Optics Silicon (Si) Aspheric Lens

DWG NO

24883

SHEET  
3 OF 19