





FOCAL LENGTH (EFL): 12 ±0,12
BACK FOCAL LENGTH (BFL): 10,63

1 532nm V-COAT
R(ABS) < 0,25% @ 532nm @ 0° AOI

LEFT SURFACE			MATERIAL		RIGHT SURFACE		
R 5,5 CX Øe 5,4 SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -			GLASS Fused Silica 458/678 Nd: 1,458		R ∞ PL Øe 5,4 SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 2,18' 5/ 40 - 20 6/ -		
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics® 6mm Dia x 12mm FL, 532NM V-COAT Coated, Plano-Convex Lens		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN: mm		TITLE		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING					DWG NO 25863		
INDICATIONS IN ACCORDANCE WITH ISO 10110					SHEET T SIZE A4		SHEET 1 OF 1