





f' : $7 \pm 0,07$

BACK FOCAL LENGTH (BFL): 5,5



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 5,5 CX Øe 6,3 λ AR Rave(350nm - 700nm, 0°) ≤ 0,50% 3/ 3 (0,5) λ=632,8 nm 4/ 3,82' 5/ 40 - 20 6/ - 			GLASS N-SF11 785/258 Nd: 1,785 Vd: 25,68	R ∞ PL Øe 6,3 λ AR Rave(350nm - 700nm, 0°) ≤ 0,50% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - 		
PROTECTIVE CHAMFERS AS NEEDED				Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm	Edmund Optics®			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY						
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			7mm Dia x 7mm FL, VIS-EXT Coated, Plano-Convex Lens			
INDICATIONS IN ACCORDANCE WITH ISO 10110			71297			
FIRST ANGLE PROJECTION 			TITLE			
ALL DIMS IN: mm			SHEET SIZE A4			
			SHEET 1 OF 1			