




$f'$ :  $12 \pm 0,12$

BACK FOCAL LENGTH (BFL): 10,3



| LEFT SURFACE                                                                                                                                                                                                                                                                                                                                                          |                |             | MATERIAL                                                                            | RIGHT SURFACE                                                                                                                                                                                                                                                               |                                    |             |                                                                                                                                  |                                                                                                               |  |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|-------------|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------|-------------|----------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------|--|
| <div>R 6,2 CX</div> <div>Øe 6,3</div> <div>⌘ AR Rave(350nm - 700nm, 0°) ≤ 0,50%</div> <div>3/ 3 (0,5) λ=632,8 nm</div> <div>4/ 1,93'</div> <div>5/ 40 - 20</div> <div>6/ -</div> <div></div>                                                                                       |                |             | <div>GLASS</div> <div>N-BK7 517/642</div> <div>Nd: 1,517</div> <div>Vd: 64,17</div> | <div>R ∞ PL</div> <div>Øe 6,3</div> <div>⌘ AR Rave(350nm - 700nm, 0°) ≤ 0,50%</div> <div>3/ 3 (0,5) λ=632,8 nm</div> <div>4/ -</div> <div>5/ 40 - 20</div> <div>6/ -</div> <div></div> |                                    |             |                                                                                                                                  |                                                                                                               |  |
| <div>PROTECTIVE CHAMFERS AS NEEDED</div> <table><tr><td>ROHS:<br/>COMPLIANT</td><td>SCALE:<br/>NONE</td><td>λ = 587,6nm</td></tr></table> <div>SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY</div> <div>FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING</div> <div>INDICATIONS IN ACCORDANCE WITH ISO 10110</div> |                |             |                                                                                     | ROHS:<br>COMPLIANT                                                                                                                                                                                                                                                          | SCALE:<br>NONE                     | λ = 587,6nm | <div>FIRST ANGLE PROJECTION</div> <div></div> | <div> Edmund Optics®</div> |  |
| ROHS:<br>COMPLIANT                                                                                                                                                                                                                                                                                                                                                    | SCALE:<br>NONE | λ = 587,6nm |                                                                                     |                                                                                                                                                                                                                                                                             |                                    |             |                                                                                                                                  |                                                                                                               |  |
|                                                                                                                                                                                                                                                                                                                                                                       |                |             | <div>TITLE</div> <div>7mm Dia x 12mm FL, VIS-EXT Coated, Plano-Convex Lens</div>    |                                                                                                                                                                                                                                                                             |                                    |             |                                                                                                                                  |                                                                                                               |  |
|                                                                                                                                                                                                                                                                                                                                                                       |                |             | <div>DWG NO</div> <div>71311</div>                                                  | <div>SHEET SIZE</div> <div>A4</div>                                                                                                                                                                                                                                         | <div>SHEET</div> <div>1 OF 1</div> |             |                                                                                                                                  |                                                                                                               |  |