




FOCAL LENGTH (EFL): 30 ±0,3

BACK FOCAL LENGTH (BFL): 27,56

- 1 785nm V-COAT  
R(ABS) < 0,25% @ 785nm @ 0° AOI

| LEFT SURFACE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            | MATERIAL                                | RIGHT SURFACE                                                                                |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------|----------------------------------------------------------------------------------------------|
| R 13,754 CX<br>Øe 11<br>(λ) SEE NOTE 1<br>3/ 3 (0,5) λ=632,8 nm<br>4/ -<br>5/ 40 - 20<br>6/ -                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | GLASS Fused Silica 458/678<br>Nd: 1,458 | R ∞ PL<br>Øe 11<br>(λ) SEE NOTE 1<br>3/ 3 (0,5) λ=632,8 nm<br>4/ 2,18'<br>5/ 40 - 20<br>6/ - |
| <div> <div> PROTECTIVE CHAMFERS AS NEEDED <div> <div>ROHS: COMPLIANT</div> <div>SCALE: NONE</div> <div>λ = 587,6nm</div> </div> </div> <div> SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY.<br/> FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING </div> </div> <div> FIRST ANGLE PROJECTION </div> <div> ALL DIMS IN: mm </div> <div> <div> <div> <div>ED</div> <div>Edmund Optics®</div> </div> <div> <div>TITLE</div> <div>12mm Dia x 30mm FL, 785NM V-COAT Coated, Plano-Convex Lens</div> </div> <div> <div>DWG NO</div> <div>25909</div> </div> <div> <div>SHEET SIZE</div> <div>A4</div> </div> <div> <div>SHEET</div> <div>1 OF 1</div> </div> </div> </div> |                                         |                                                                                              |