





FOCAL LENGTH (EFL): 50 ± 0,5
BACK FOCAL LENGTH (BFL): 46

- 1 785nm V-COAT
R(ABS) < 0,25% @ 785nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE			
R 22,923 CX			GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL			
Øe 24				Øe 24			
⌂ SEE NOTE 1				⌂ SEE NOTE 1			
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm			
4/ -				4/ 2,18'			
5/ 40 - 20				5/ 40 - 20			
6/ -			6/ -				
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	25mm Dia x 50mm FL, 785NM V- COAT Coated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				ALL DIMS IN:	mm	DWG NO	25914
INDICATIONS IN ACCORDANCE WITH ISO 10110			SHEET T SIZE A4				SHEET 1 OF 1