






f': 8 ±0,08

BACK FOCAL LENGTH (BFL): 6,4



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 6,28 CX Øe 7,2 ⌈λ⌋ AR R(880nm, 0°) ≤ 0,25% Rave(400nm - 870nm, 0°) ≤ 1,25% Rave(890nm - 1000nm, 0°) ≤ 1,25% 3/ 3 (0,5) λ=632,8 nm 4/ 3,82' 5/ 40 - 20 6/ - 			GLASS N-SF11 785/258 Nd: 1,785 Vd: 25,68	R ∞ PL Øe 7,2 ⌈λ⌋ AR R(880nm, 0°) ≤ 0,25% Rave(400nm - 870nm, 0°) ≤ 1,25% Rave(890nm - 1000nm, 0°) ≤ 1,25% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - 		
PROTECTIVE CHAMFERS AS NEEDED						
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY						
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	TITLE 8mm Dia x 8mm FL, VIS-NIR Coated, Plano-Convex Lens	
			DWG NO	71319	SHEET SIZE A4	SHEET 1 OF 1