





FOCAL LENGTH (EFL): 200 ±2

BACK FOCAL LENGTH (BFL): 198,02

- 1 785nm V-COAT  
R(ABS) < 0,25% @ 785nm @ 0° AOI

| LEFT SURFACE                                                                                  | MATERIAL                                | RIGHT SURFACE                                                                                |
|-----------------------------------------------------------------------------------------------|-----------------------------------------|----------------------------------------------------------------------------------------------|
| R 91,692 CX<br>Øe 24<br>(λ) SEE NOTE 1<br>3/ 3 (0,5) λ=632,8 nm<br>4/ -<br>5/ 40 - 20<br>6/ - | GLASS Fused Silica 458/678<br>Nd: 1,458 | R ∞ PL<br>Øe 24<br>(λ) SEE NOTE 1<br>3/ 3 (0,5) λ=632,8 nm<br>4/ 2,18'<br>5/ 40 - 20<br>6/ - |

|                                                                                          |                |             |                                                                                     |                                                                                                    |                                                                 |                    |
|------------------------------------------------------------------------------------------|----------------|-------------|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------|-----------------------------------------------------------------|--------------------|
| PROTECTIVE CHAMFERS AS NEEDED                                                            |                |             | FIRST ANGLE<br>PROJECTION                                                           |  Edmund Optics® |                                                                 |                    |
| ROHS:<br>COMPLIANT                                                                       | SCALE:<br>NONE | λ = 587,6nm |                                                                                     |                                                                                                    |                                                                 |                    |
| SPECIFICATIONS SUBJECT TO CHANGE<br>WITHOUT NOTICE. DIMENSIONS ARE FOR<br>REFERENCE ONLY |                |             |  | TITLE                                                                                              | 25mm Dia x 200mm FL, 785NM V-<br>COAT Coated, Plano-Convex Lens |                    |
| FOR INFORMATION ONLY: DO NOT<br>MANUFACTURE PARTS TO THIS DRAWING                        |                |             |                                                                                     | DWG NO                                                                                             | 25920                                                           | SHEET<br>T SIZE A4 |
| INDICATIONS IN ACCORDANCE WITH ISO 10110                                                 |                |             | ALL<br>DIMS IN: mm                                                                  |                                                                                                    |                                                                 | SHEET<br>1 OF 1    |