




f' : $12 \pm 0,12$

BACK FOCAL LENGTH (BFL): 10



LEFT SURFACE			MATERIAL	RIGHT SURFACE														
R 6,2 CX Øe 7,2 ⌘ AR R(880nm, 0°) ≤ 0,25% Rave(400nm - 870nm, 0°) ≤ 1,25% Rave(890nm - 1000nm, 0°) ≤ 1,25% 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ - 			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 7,2 ⌘ AR R(880nm, 0°) ≤ 0,25% Rave(400nm - 870nm, 0°) ≤ 1,25% Rave(890nm - 1000nm, 0°) ≤ 1,25% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - 														
PROTECTIVE CHAMFERS AS NEEDED <table><tr><td>ROHS: COMPLIANT</td><td>SCALE: NONE</td><td>λ = 587,6nm</td></tr></table> SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110			ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm	FIRST ANGLE PROJECTION  ALL DIMS IN: mm	 Edmund Optics® <table><tr><td>TITLE</td><td colspan="2">8mm Dia x 12mm FL, VIS-NIR Coated, Plano-Convex Lens</td></tr><tr><td>DWG NO</td><td>71333</td><td></td></tr></table> <table><tr><td>SHEET SIZE</td><td>A4</td><td>SHEET 1 OF 1</td></tr></table>			TITLE	8mm Dia x 12mm FL, VIS-NIR Coated, Plano-Convex Lens		DWG NO	71333		SHEET SIZE	A4	SHEET 1 OF 1
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm																
TITLE	8mm Dia x 12mm FL, VIS-NIR Coated, Plano-Convex Lens																	
DWG NO	71333																	
SHEET SIZE	A4	SHEET 1 OF 1																