





f: 76,2 ±0,76

BACK FOCAL LENGTH (BFL): 68,948



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 39,38 CX Øe 49,3 ⌂ AR Rave(400nm - 700nm, 0°) < 1,75% 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ - P			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 49,3 ⌂ AR Rave(400nm - 700nm, 0°) < 1,75% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - P		
PROTECTIVE CHAMFERS AS NEEDED				Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm	FIRST ANGLE PROJECTION			⊕
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			50,8mm Dia x 76,1997mm FL, MgF2 Coated, Plano-Convex Lens			
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	71342
			SHEET SIZE			A4
			SHEET			1 OF 1