

FORGE[®] 5GIGE CAMERAS

FG-P5G-161S7

Measurements are taken based on guidelines in the EMVA 1288 standard; the full definition can be found at EMVA.org. Camera settings are: maximum bit depth, 16-bit pixel format, and ISP disabled. The center wavelength is 525 nm unless otherwise noted. Results are captured at room temperature (20°C).


	Forge FG-P5G-161S7M	Forge FG-P5G-161S7C
Resolution	5320x3032	5320x3032
Sensor	Sony IMX542, CMOS, 1.1	Sony IMX542, CMOS, 1.1
Pixel Size (µm)	2.74	2.74
Firmware Version	2110.1.906.0	2110.1.906.0
ADC Bit Depth	12	12
Quantum Efficiency Mono (% at 525 nm)	68.52	N/A
Quantum Efficiency Blue (% at 470 nm)	N/A	46.73
Quantum Efficiency Green (% at 525 nm)	N/A	53.66
Quantum Efficiency Red (% at 630 nm)	N/A	34.11
Temporal Dark Noise (Read Noise) (e-)	2.23	2.32
Temporal Dark Noise (Read Noise) (DN)	15.53	15.91
Signal to Noise Ratio Maximum (dB)	39.87	39.76
Signal to Noise Ratio Maximum (Bits)	6.62	6.60
Absolute Sensitivity Threshold (γ)	4.14	5.45
Absolute Sensitivity Threshold (e-)	2.84	2.92
Saturation Capacity (Well Depth) (e-)	9701	9466
Saturation Capacity (Well Depth) (γ)	14158	17657
Dynamic Range (dB)	70.68	70.21
Dynamic Range (Bits)	11.74	11.66
Gain (e-/ADU)	0.15	0.15

11/25/2024


Names and marks appearing on the products herein are either registered trademarks or trademarks of FLIR Integrated Imaging Solutions Inc. and/or its subsidiaries.

© 2016-2024 FLIR Integrated Imaging Solutions Inc. All rights reserved. This document does not contain export-controlled information.

Forge FG-P5G-161S7M Spectral Response Curve



Forge FG-P5G-161S7C Spectral Response Curve



11/25/2024

Names and marks appearing on the products herein are either registered trademarks or trademarks of FLIR Integrated Imaging Solutions Inc. and/or its subsidiaries.

© 2016-2024 FLIR Integrated Imaging Solutions Inc. All rights reserved. This document does not contain export-controlled information.