

[Afficher tous les 259 produits de la même famille.](#)

TECHSPEC® Fenêtre  $\lambda/10$  en Silice Fondue Traitée VIS 0°, 100 mm de dia., 5 mm d'épaisseur



Stock #22-067 10 In Stock

-

1

+

€905<sup>,00</sup>

AJOUTER AU PANIER

| Prix sur Quantité |                                  |
|-------------------|----------------------------------|
| Qté 1-5           | €905,00 prix unitaire            |
| Qté 6-25          | €720,00 prix unitaire            |
| Qté 26-49         | €675,00 prix unitaire            |
| Need More?        | <a href="#">Demande de Devis</a> |

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Caractéristiques du produit

Type:

Protective Window

Propriétés physiques et mécaniques

Ouverture Utile CA (mm):

90.00

Diamètre (mm):

100.00 +0.00/-0.20

|                      |                                     |
|----------------------|-------------------------------------|
| 5.00 ±0.10           | Épaisseur (mm):                     |
| Protective as needed | Biseau:                             |
| 90                   | Ouverture Utile (%):                |
| Fine Ground          | Bords:                              |
| <10                  | Parallélisme (arcsec):              |
| 0.16                 | Rapport de Poisson:                 |
| 73                   | Module d'Élasticité de Young (GPa): |
| 522.00               | Dureté de Knoop (kg/mm²):           |

Propriétés optiques

|                                              |                                         |
|----------------------------------------------|-----------------------------------------|
| VIS 0° (425-675nm)                           | Traitement:                             |
| <a href="#">Fused Silica</a> (Corning 7980)  | Substrat: □                             |
| 1.458                                        | Indice de Réfraction (n <sub>d</sub> ): |
| 40-20                                        | Qualité de Surface:                     |
| <i>N</i> 10 (per inch within clear aperture) | Front d'Onde Transmis, P-V:             |
| 67.8                                         | Nombre d'Abbe (v <sub>d</sub> ):        |
| R <sub>avg</sub> ≤0.4% @ 425 - 675nm         | Spécification du Traitement:            |
| 425 - 675                                    | Gamme de Longueur d'Onde (nm):          |
| 5 J/cm² @ 532nm, 10ns                        | Damage Threshold, Reference:            |

Propriétés des matériaux

|                                                                   |                                                               |
|-------------------------------------------------------------------|---------------------------------------------------------------|
| 2.20                                                              | Densité (g/cm³):                                              |
| 0.52 (+5 to +35°C)<br>0.57 (0 to +200°C)<br>0.48 (-100 to +200°C) | Coefficient d'Expansion Thermique CTE (10 <sup>-6</sup> /°C): |
| 7980 0G                                                           | Fused Silica Grade:                                           |

Conformité réglementaire

|                           |                             |
|---------------------------|-----------------------------|
| <a href="#">Conforme</a>  | RoHS 2015:                  |
| <a href="#">Visionner</a> | Certificate of Conformance: |
| <a href="#">Conforme</a>  | Reach 235:                  |

Description produit

• Versions traitées antireflets UV-VIS et UV disponibles

• Distorsion du front d'onde transmis *N*/10

• Dimensions allant de 5 à 150 mm de diamètre

• Fenêtres en Silice Fondue [1λ](#) ou [λ/4](#) également disponibles

Nos Fenêtres *N*/10 en Silice Fondue UV TECHSPEC® se caractérisent par un parallélisme et une qualité de surface indice laser. Par ailleurs, ces fenêtres limiteront la distorsion du front d'onde transmis à *N*/10. Les caractéristiques de transmission supérieures, les excellentes propriétés thermiques et les spécifications de fabrication haute tolérance font de ces fenêtres un excellent choix pour les applications plus exigeantes. Les Fenêtres *N*/10 en Silice Fondue UV TECHSPEC sont disponibles dans des tailles allant de 5 à 150 mm de diamètre. Ces fenêtres sont offertes sans traitement ou avec des traitements anti-reflets optimisés pour le spectre UV ou visible.

Informations techniques



FUSED SILICA

Uncoated Fused Silica  
Typical Transmission



Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.

[Click Here to Download Data](#)

Fused Silica with MgF<sub>2</sub> Coating  
Typical Transmission



Typical transmission of a 3mm thick fused silica window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 1.75\% \text{ @ } 400 - 700\text{nm (N-BK7)}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Fused Silica with UV-AR Coating  
Typical Transmission



Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 1.0\% \text{ @ } 250 - 425\text{nm}$$

$$R_{avg} \leq 0.75\% \text{ @ } 250 - 425\text{nm}$$

$$R_{avg} \leq 0.5\% \text{ @ } 370 - 420\text{nm}$$


Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Fused Silica with UV-VIS Coating  
Typical Transmission



|                                                                                                                                                                       |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                      | <p>Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 1.0\%</math> @ 350 - 450nm<br/><math>R_{avg} \leq 1.5\%</math> @ 250 - 700nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                   |
| <p><b>Fused Silica with VIS-EXT Coating</b><br/><b>Typical Transmission</b></p>    | <p>Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.5\%</math> @ 350 - 700nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                    |
| <p><b>Fused Silica with VIS-NIR Coating</b><br/><b>Typical Transmission</b></p>   | <p>Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 0.25\%</math> @ 880nm<br/><math>R_{avg} \leq 1.25\%</math> @ 400 - 870nm<br/><math>R_{avg} \leq 1.25\%</math> @ 890 - 1000nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p> |
| <p><b>Fused Silica with VIS 0° Coating</b><br/><b>Typical Transmission</b></p>    | <p>Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.4\%</math> @ 425 - 675nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                     |
| <p><b>Fused Silica with YAG-BBAR Coating</b><br/><b>Typical Transmission</b></p>  | <p>Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.5\%</math> @ 500 - 1100nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                 |



$R_{abs} \leq 0.25\% \text{ @ } 532\text{nm}$   
 $R_{abs} \leq 0.25\% \text{ @ } 1064\text{nm}$   
 $R_{avg} \leq 1.0\% \text{ @ } 500 - 1100\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick fused silica window with NIR  
I (600 - 1050nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% @ 600 - 1050nm$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick fused silica window with NIR  
II (750 - 1550nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

 $R_{\text{abs}} \leq 1.5\% @ 750 - 800\text{nm}$  $R_{\text{abs}} \leq 1.0\% @ 800 - 1550\text{nm}$ 
$$R_{avg} \leq 0.7\% @ 750 - 1550\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

## Coating Curves

## Sur mesure

Edmund Optics propose des services complets de fabrication personnalisée de composants optiques et d'imagerie adaptés aux exigences de vos applications spécifiques. Qu'il s'agisse de la phase de prototypage ou de la préparation d'une production à grande échelle, nous proposons des solutions flexibles pour répondre à vos besoins. Nos ingénieurs expérimentés sont là pour vous aider, de la conception à la réalisation.

Nos capacités comprennent :

- Dimensions, matériaux, traitements, etc. personnalisés
- Qualité de surface et planéité de surface de haute précision
- Tolérances serrées et géométries complexes
- Production évolutive – du prototype à la série

En savoir plus sur nos [capacités de fabrication sur mesure](#) ou soumettre une demande [ici](#).

## Montures compatibles