





NOTES:

- 1. SUBSTRATE: Fused Silica
- 2. COATING (APPLY ACROSS CLEAR APERTURE)


S1&S2: Ravg ≤0.5% @ 600 - 1050nm
- 3.  ARROW POINTS TOWARD TILTED SURFACE
- 4.  FINE GRIND SURFACE
- 5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
- 6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
RADIUS	INFINITY	INFINITY
MINI CLEAR APERTURE	Ø 22.50	Ø 22.50
SURFACE QUALITY	20-10	20-10
SURFACE ACCURACY	λ/10	λ/10
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	25mm Dia., NIR I Coated, 30' Wedge, Fused Silica Wedged Window
ALL DIMS IN	mm	DWG NO	25619
			SHEET 5 OF 15