

In series


The model is in series and available for the long term.



Specification

Sensor

Sensor type	CMOS Color
Shutter	Global Shutter
Sensor characteristic	Linear
Readout mode	Progressive scan
Pixel Class	8 MP
Resolution	8.13 Mpix
Resolution (h x v)	2856 x 2848 Pixel
Aspect ratio	1:1
ADC	12 bit
Color depth (camera)	12 bit
Optical sensor class	2/3"
Optical Size	7.825 mm x 7.804 mm
Optical sensor diagonal	11.05 mm (1/1.45")
Pixel size	2.74 µm
Manufacturer	Sony
Sensor Model	IMX536AAQJ-C
Gain (master/RGB)	15.9x/16x
AOI horizontal	same frame rate
AOI vertical	increased frame rate
AOI image width / step width	256 / 2
AOI image height / step width	2 / 2
AOI position grid (horizontal/vertical)	2 / 2
Binning horizontal	same frame rate
Binning vertical	same frame rate
Binning method	M/C automatic
Binning factor	2 / 4 / 8
Subsampling horizontal	same frame rate
Subsampling vertical	same frame rate
Subsampling method	M/C automatic
Subsampling factor	2, 4, 8



Model

Frame rate freerun mode (in 8-bit mode)	146 fps
Frame rate trigger (continuous)	146 fps
Frame rate trigger (maximum)	146 fps
Exposure time (minimum - maximum)	0.009 ms - 2000 ms
Long exposure (maximum)	90000 ms
Power consumption	9.1 W - 15.4 W
Image memory	2032 MB

Ambient conditions

The temperature values given below refer to the outer device temperature of the camera housing.


Device temperature during operation	0 °C - 55 °C / 32 °F - 131 °F
Device temperature during storage	-20 °C - 60 °C / -4 °F - 140 °F
Humidity (relative, non-condensing)	20 % - 80 %

Connectors

Interface connector	GigE RJ45, screwable
I/O connector	12-pin M12 connector (Attend 216A-12MSR)
Power supply	12 V - 24 V or PoE+

Pin assignment I/O connector

1	Power supply, 12-24 V DC
2	Power supply, ground
3	(Trigger) input 0 with optocoupler - Line0
4	Reference level for all optocoupler outputs
5	Reference level for all optocoupler inputs
6	(Trigger) input 1 with optocoupler - Line1
7	(Flash) output 1 with optocoupler - Line4
8	Fast (flash) output 2 with optocoupler - Line5
9	Power supply for fast (flash) outputs, 3-5 V DC
10	Fast (flash) output 3 with optocoupler - Line6
11	(Trigger) input 2 with optocoupler - Line2
12	(Flash) output 0 with optocoupler - Line3



Design

Lens Mount	C-Mount
IP code	IP30
Dimensions H/W/L	60.0 mm x 75.0 mm x 94.5 mm
Mass	550 g

Features

Image Acquisition	Freerun	✓
	Software trigger	✓
	Hardware trigger	✓
	Trigger controlled exposure	✓
	Denoiser	✓
	Long exposure	✓
	Line scan	✓
	Line scan highspeed	-

Flashing

Flashing	✓
PWM flashing	✓

Image Adjustments

Auto exposure	✓
Auto gain	✓
Auto whitebalance	✓
Color correction	✓
Gamma	✓
LUT	✓
Mirror/flip	X/Y

On-board Image Processing

Pixel formats	Mono8 BayerRG8 BayerRG10 BayerRG10p BayerRG12 BayerRG12p BGR8 RGB8 BGR10p32 RGB10p32
Region of interest	✓
Decimation (FPGA)	✓
Decimation (Sensor)	2x2
Binning (FPGA)	✓
Binning (Sensor)	-

Others

IP settings	✓
Bandwidth management	✓
Chunks	✓
Sequencer	✓
PTP	-
Firmware update	✓
1st supported firmware version	3.6