





FOCAL LENGTH (EFL): 76,2 ± 0,76

BACK FOCAL LENGTH (BFL): 68,948

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R 39,38 CX Øe 49,3 (λ) - 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -		GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 49,3 (λ) - 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ -	
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110		FIRST ANGLE PROJECTION  ALL DIMS IN: mm	 Edmund Optics® TITLE 50,8mm Dia x 76,20mm FL, Uncoated, Plano-Convex Lens DWG NO 29095 SHEET SIZE A4 SHEET 1 OF 1	