




f' : $10 \pm 0,1$

BACK FOCAL LENGTH (BFL): 8,1



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 5,17 CX			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL		
Øe 6,3				Øe 6,3		
λ AR Rave(350nm - 700nm, 0°) ≤ 0,50%				λ AR Rave(350nm - 700nm, 0°) ≤ 0,50%		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ 5,8'				4/ -		
5/ 40 - 20			5/ 40 - 20			
6/ -			6/ -			
						
PROTECTIVE CHAMFERS AS NEEDED			 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE 7mm Dia x 10mm FL, VIS-EXT Coated, Plano-Convex Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			DWG NO 71304			
			SHEET SIZE A4			
ALL DIMS IN: mm			SHEET 1 OF 1			