





f' : $10 \pm 0,1$

BACK FOCAL LENGTH (BFL): 8,1



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 5,17 CX Øe 6,3 λ AR R(532nm, 0°) < 0,25% R(1064nm, 0°) < 0,25% Rave(500nm - 1100nm, 0°) < 1,00% 3/ 3 (0,5) λ=632,8 nm 4/ 5,8' 5/ 40 - 20 6/ - 			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 6,3 λ AR R(532nm, 0°) < 0,25% R(1064nm, 0°) < 0,25% Rave(500nm - 1100nm, 0°) < 1,00% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - 		
PROTECTIVE CHAMFERS AS NEEDED				Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm	Edmund Optics®			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY						
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			7mm Dia x 10mm FL, YAG-BBAR Coated, Plano-Convex Lens			
INDICATIONS IN ACCORDANCE WITH ISO 10110			71306			
FIRST ANGLE PROJECTION			TITLE			
ALL DIMS IN: mm			DWG NO			
			SHEET SIZE A4			
			SHEET 1 OF 1			