




f' : $12 \pm 0,12$

BACK FOCAL LENGTH (BFL): 10



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 6,2 CX Øe 7,2 λ AR R(750nm - 800nm, 0°) ≤ 1,50% R(800nm - 1550nm, 0°) ≤ 1,00% Rave(750nm - 1550nm, 0°) ≤ 0,70% 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ - 			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 7,2 λ AR R(750nm - 800nm, 0°) ≤ 1,50% R(800nm - 1550nm, 0°) ≤ 1,00% Rave(750nm - 1550nm, 0°) ≤ 0,70% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - 		
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110				FIRST ANGLE PROJECTION  ALL DIMS IN: mm	 Edmund Optics® TITLE 8mm Dia x 12mm FL, NIR II Coated, Plano-Convex Lens DWG NO 71331 SHEET SIZE A4 SHEET 1 OF 1	