





f': 76,2 ±0,76

BACK FOCAL LENGTH (BFL): 68,948



LEFT SURFACE			MATERIAL	RIGHT SURFACE					
R 39,38 CX Øe 49,3 λ AR Rave(350nm - 700nm, 0°) ≤ 0,50% 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ - P			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 49,3 λ AR Rave(350nm - 700nm, 0°) ≤ 0,50% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - P					
PROTECTIVE CHAMFERS AS NEEDED <table><tr><td>ROHS: COMPLIANT</td><td>SCALE: NONE</td><td>λ = 587,6nm</td></tr></table> SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110				ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm	FIRST ANGLE PROJECTION	EO ® Edmund Optics®	
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm							
			TITLE	50,8mm Dia x 76,1997mm FL, VIS-EXT Coated, Plano-Convex Lens					
			ALL DIMS IN: mm	DWG NO	71346				
				SHEET SIZE	A4	SHEET 1 OF 1			