





f': 76,2 ±0,76

BACK FOCAL LENGTH (BFL): 68,948



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 39,38 CX Øe 49,3 λ AR R(532nm, 0°) < 0,25% R(1064nm, 0°) < 0,25% Rave(500nm - 1100nm, 0°) < 1,00% 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ - P			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 49,3 λ AR R(532nm, 0°) < 0,25% R(1064nm, 0°) < 0,25% Rave(500nm - 1100nm, 0°) < 1,00% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - P		
PROTECTIVE CHAMFERS AS NEEDED				 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY						TITLE 50,8mm Dia x 76,1997mm FL, YAG-BBAR Coated, Plano-Convex Lens
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			DWG NO 71348			
INDICATIONS IN ACCORDANCE WITH ISO 10110						SHEET SIZE A4
			SHEET 1 OF 1			