

NOTES:




1. SUBSTRATE: FLOAT GLASS

3. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: BBAR (425-700nm)  
R(AVG) ≤0.5% @ 425 - 700nm

 FINE GRIND SURFACE

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80 - 50	80 - 50
CLEAR APERTURE	11.43 x 11.43	11.43 x 11.43
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED



ALL DIMS IN mm

 **Edmund Optics®**

TITLE	12.70 x 12.70 x 1mm High Efficiency Window		
DWG NO	71582	SHEET	6 OF 6