

[Afficher tous les 20 produits de la même famille.](#)

Adaptateur de Monture C 0,5X pour Unités de Microscope Vidéo Mitutoyo

See More by [Mitutoyo](#)



Stock **#71-006** 1 In Stock

-

1

+

€2.320⁰⁰

AJOUTER AU PANIER

Prix sur Quantité	
Qté 1+	€2.320,00 prix unitaire
Need More?	Demande de Devis

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Propriétés physiques et mécaniques

25

Poids (g):

Propriétés optiques

0.5X

Grossisse-
ment:

Capteur

Type de Capteur:

- Conçus pour les **Objectifs Corrigés à l'Infini** M26 x36 TPI ou M40 x36
- Taille maximale du capteur de 2/3" ou APS-C
- Orientations verticales et horizontales, configurations fond clair et fond noir disponibles
- Port d'éclairage en ligne par fibre optique, compatible avec des férules un diamètre de 8 mm ou 1/4" (0,312")

Les Unités de Microscope Vidéo (VMU) de Mitutoyo (VMU) sont utilisées pour relier les **objectifs corrigés à l'infini** à **une caméra de monture C ou F** afin d'obtenir un système de microscopie de manière facile et rapide. Apportant un grossissement de 1X, cette unité comporte un port d'éclairage en ligne pour un contraste maximum et un éclairage simple par rapport à des techniques en éclairage épi. Les configurations VMU à fond clair sont équipées d'un iris réglable permettant de contrôler le flux de lumière sans ajuster l'obturateur ou le gain de la caméra.

Des tourelles manuelles Mtutoyo sont disponibles pour chaque configuration VMJ. Elles présentent quatre montures d'objectifs qui permettent de changer rapidement les différents objectifs de différents grossissements. En associant la tourelle à la VMJ, on obtient un système flexible de microscope à imagerie vidéo.

Horizontal VIS-NIR VMU (#89-621)

Technical drawings of the Horizontal VIS-NIR VMU (#89-621) showing front, side, and detail views with dimensions in millimeters.

Front View Dimensions:

- Overall Width: 83.5
- Image Position: 60
- F-Mount: 46.5
- Overall Height: 380.2
- Top Section Height: 146.2
- Section Height: 54
- Section Height: 85
- Parfocal Length: 95
- Workpiece Surface
- Objective Mount
- Objective (Optional)
- 4-Max 0.7 depth 6 Same position and number on the other side
- Fiber Mounting Position
- 285.2
- 146.2
- 50

Side View Dimensions:

- Overall Width: 64
- Overall Height: 426.7
- Workpiece Surface

Detail View Dimensions:

- Fiber Mounting Portion
- Fiber Spun: $\varnothing 14$
- Hexagon Socket Set Screw (M4) for clamping fiber light guide
- Fiber Edge Position
- 19
- 2
- 12.0




Front View Dimensions (Bottom):

- Overall Width: 63
- Section Width: 59.5
- Section Width: 19
- Section Width: 50
- Section Width: 27
- Section Width: 43.5
- Section Width: 27
- Section Width: 76
- Section Width: 20.5
- Section Width: 106
- Section Width: 47
- Section Width: 208.5
- Section Width: 113.5
- Section Width: 80.5
- Section Width: 35
- Section Width: 95
- Parfocal Distance
- Workpiece Surface
- Objective (sold separately)
- $\varnothing 43$

Side View Dimensions (Bottom):

- Overall Width: 47
- Workpiece Surface

Units: mm



Mitutoyo Video Microscope Unit (VMU) and Mitutoyo Turret						
Wavelength Range:	VIS-NIR		NUV-VIS-NIR Nd:YAG 355/532/1064nm	VIS-NIR-SWIR Widefield Hi-Res	VIS Widefield BD	
Type:	Brightfield		Brightfield	Brightfield	Brightfield/Darkfield	
Orientation:	Vertical	Horizontal	Vertical	Vertical	Vertical	Horizontal
Model:	378-505	378-506	378-507	378-519	378-517	378-518
Tube Lens Magnification:	1X		1X	1X	1X	
Camera Mount:	C-Mbunt		C-Mbunt	F-Mbunt or C-Mbunt w/included adapter	F-Mbunt or C-Mbunt w/included adapter	
Objective Mount:	M26 x 36 TPI		M26 x 36 TPI	M26 x 36 TPI	M40 x 36 TPI	
Max. Sensor Format:	2/3"		2/3"	APS-C	APS-C	
Weight:	570g	590g	980g	1400g	2150g	
Stock Number:	#86-799	#89-621	#89-622	#23-338	#18-653	
Manual Turret (Four Objective Mounts):	#86-589		#86-589	#18-654	#18-655	
Compatible Objectives:	MPlan Apo/HR/SL and G Plan Apo		MPlan Apo/HR/SL and MPlan NIR/NUV	MPlan Apo/HR/SL G Plan Apo MPlan Apo NIR	BD Plan Apo	
VMU-L Laser Mount to C-Mount Adapter:	N/A		#37-044	N/A	N/A	