

In order to provide more accurate inventory information, please select your shipping country.

Sélectionner votre Pays/Région:

European Union

SUBMIT

Stock #19-014

FIN DE SÉRIE

3-4 JOURS

- 1 +

€9,95

AJOUTER AU PANIER

Qté 1+

€9,95

Prix sur Quantité

[Demande de Devis](#)

Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Rapport d'Extinction:

9000:1 (nominal at 555nm)

Substrat:

[Polymer Film XP42-75](#)

Température d'Utilisation (°C):

-40 to +80

Dimensions (mm):

25.0 x 25.0

Épaisseur (mm):

0.77 ±0.08

Transmission (%) : Single: 42 ±2 Parallel: 36.4 Crossed: <0.004 (nominal at 555nm)
Type : Linear Polarizer
Tolérance Dimensionelle (mm) : ±0.5
Construction : Polarizing Film
Remarque : Polarization axis can be identified as follows: Circular Parts - Parallel to direction of notch on polarizer Square Parts - Parallel to mark on protective film Rectangular Parts - Parallel to first listed dimension
Gamme de Longueur d'Onde (nm) : 400 - 700
Efficacité de la polarisation (%) : >99.98 (nominal at 555nm)
Transmission Variance after 1000 Hours (%) : <±5
#Sorting : 28.00

Conformité réglementaire

RoHS 2015 : Conforme
Certificate of Conformance : Visionner
Reach 235 : Conforme