

In order to provide more accurate inventory information, please select your shipping country:

Sélectionner votre Pays/Région: European Union

SUBMIT

Kit de Developpement pour Lentilles Liquides a Focalisation variable Corning® Varioptic®, ouverture utile de 2,5 mm, traitement VIS, plage de mise au point de 70 dioptries



2.5mm CA, VIS Coated, 70 Diopter Focus Range, Corning® Varioptic® Variable Focus Liquid Lens Development Kit



Stock #19-357 FIN DE SÉRIE 3-4 JOURS

- 1 +

€601,95

AJOUTER AU PANIER

Qté 1+

€601,95

Prix sur Quantité

[Demande de Devis](#)

Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement



Diamètre (mm):
9.40 (packaged lens, 7.75 bare lens)

Traitement: VS
Type: Development Kit
Ouverture Utile CA (mm): 2.5
Contenu du Coffret: Coming® Varioptic® A-25H0-D0 Lens (without cable) A-25H0-D0-P07 Lens (with straight flex cable : 4 pins) Maxim MAX14574 Driver Board (with 4 pin connector and 6 pin connector for thermistor populated 6 pin FPC) USB-MFlexiboard (with 4 and 6 pin connector and USB compatibility) M4 thread holder for lens Bent Flex Cable FPC-A-03 Control Software Documentation Package
Gamme de Focalisation: -35 to +35 diopter
Numéro de Modèle: D-A-25H0-D0
Température d'Utilisation (°C): -20 to +60
Température de Stockage (°C): -40 to +85
Épaisseur (mm): 3.50 (packaged lens, 2.15 bare lens)
Transmission (%): 96 @ 587nm
Erreur du Front d'Onde Transmis, RMS: 70nm
Applications Typiques: Very close auto-focus or continuous auto-focus applications in portable devices and in laser or lighting applications for variable focus and expansion control. Features 3X higher dynamic range over the A-25HX lens.

Conformité réglementaire

RoHS 2015: Conforme
Reach 224: Conforme
Certificate of Conformance: Visionner
