

[Afficher tous les 239 produits de la même famille.](#)

TECHSPEC<sup>®</sup> Lentille Plan-Convexe Traitée MgF<sub>2</sub>, 6,0 mm de dia. x 10 mm FL



Stock **#38-215** 10 In Stock

[D'autres traitements](#)

-

1

+

€38<sup>.25</sup>

AJOUTER AU PANIER

| Prix sur Quantité |                                  |
|-------------------|----------------------------------|
| Qté 1-9           | €38,25 prix unitaire             |
| Qté 10-24         | €34,25 prix unitaire             |
| Qté 25-49         | €30,75 prix unitaire             |
| Need More?        | <a href="#">Demande de Devis</a> |

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Caractéristiques du produit

Plano-Convex Lens

Type:

Propriétés physiques et mécaniques

|                      |                             |
|----------------------|-----------------------------|
| 6.00 +0.0/-0.025     | Diamètre (mm):              |
| <3                   | Centrage (arcmin):          |
| 1.80 ±0.05           | Épaisseur Centrale CT (mm): |
| 0.84                 | Épaisseur au Bord ET (mm):  |
| 5.4                  | Ouverture Utile CA (mm):    |
| Protective as needed | Biseau:                     |

|                                      |                                   |
|--------------------------------------|-----------------------------------|
| Propriétés optiques                  |                                   |
| 10.00 @ 587.6nm                      | Distance Focale EFL (mm):         |
| 8.82                                 | Distance Focale Arrière BFL (mm): |
| MgF <sub>2</sub> (400-700nm)         | Traitement:                       |
| R <sub>avg</sub> ≤1.75% @400 - 700nm | Spécification du Traitement:      |
| N-BK7                                | Substrat: □                       |
| 40-20                                | Qualité de Surface:               |
| 1.5λ                                 | Power (P-V) @ 632.8nm:            |
| λ/4                                  | Irregularity (P-V) @ 632.8nm:     |
| ±1                                   | Tolérance Distance Focale (%):    |
| 5.17                                 | Rayon R <sub>1</sub> (mm):        |
| 1.67                                 | f/#:                              |
| 0.30                                 | Ouverture Numérique NA:           |
| 400 - 700                            | Gamme de Longueur d'Onde (nm):    |
| 10 J/cm <sup>2</sup> @ 532nm, 10ns   | Damage Threshold, Reference: □    |

|                          |                             |
|--------------------------|-----------------------------|
| Conformité réglementaire |                             |
| Conforme                 | RoHS 2015:                  |
| Visionner                | Certificate of Conformance: |
| Conforme                 | Reach 235:                  |

## Besoin de spécifications différentes ou de modifications ?

Edmund Optics propose des services complets de fabrication personnalisée de composants optiques et d'imagerie adaptés aux exigences de vos applications spécifiques. Qu'il s'agisse de la phase de prototypage ou de la préparation d'une production à grande échelle, nous proposons des solutions flexibles pour répondre à vos besoins. Nos ingénieurs expérimentés sont là pour vous aider, de la conception à la réalisation.

Nos capacités comprennent :

- Dimensions, matériaux, traitements, etc. personnalisés
- Qualité de surface et planéité de surface de haute précision
- Tolérances serrées et géométries complexes
- Production évolutive – du prototype à la série


En savoir plus sur nos [capacités de fabrication sur mesure](#) ou soumettre une demande [ici](#).

## Description produit

- Traitées AR pour offrir < 1,75% de réflectivité par surface entre 400 - 700 nm
- Conçues pour un angle d'incidence de 0°
- Diverses options de traitement : **Non Traitées**, **VIS 0°**, **VIS-NIR**, **NIR I**, **NIR II**, **VIS-EXT** et **YAG-BBAR**
- **Également disponibles en versions prémontées** dans des logements de monture C gravés

Les Lentilles Plan-Convexes (PCX) Traitées MgF<sub>2</sub> TECHSPEC® possèdent une distance focale positive, les rendant idéales pour recueillir et focaliser la lumière dans des applications d'imagerie. Elles sont également utiles dans une variété d'applications impliquant les émetteurs, détecteurs, lasers et fibres optiques. Les Lentilles Plan-Convexes (PCX) Traitées MgF<sub>2</sub> TECHSPEC sont disponibles dans une grande variété de diamètres et de distances focales. Des modèles identiques de ces lentilles sont également proposés **non traités** ou avec autres traitements antireflets à large bande (BBAR), qui comprennent : **VIS 0°**, **VIS-NIR**, **NIR I**, **NIR II**, **VIS-EXT** et **YAG-BBAR**.

Informations techniques



|                                                                                                           |                                                                                                                                                                                                                                                                                                                                                                                                                |
|-----------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| N-BK7                                                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                                |
| <p><b>Uncoated N-BK7 Typical Transmission</b></p> <p>T (%)</p> <p>Wavelength (nm)</p>                     | <p>Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                                                                                                              |
| <p><b>N-BK7 with MgF<sub>2</sub> Coating Typical Transmission</b></p> <p>T (%)</p> <p>Wavelength (nm)</p> | <p>Typical transmission of a 3mm thick N-BK7 window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p>R<sub>avg</sub> ≤ 1.75% @ 400 - 700nm (N-BK7)</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p> |
| <p><b>N-BK7 with VIS-EXT Coating Typical Transmission</b></p> <p>T (%)</p> <p>Wavelength (nm)</p>         | <p>Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p>R<sub>avg</sub> ≤ 0.5% @ 350 - 700nm</p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                  |

|                                                                                                                                                                                                                                                                                       |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <p>200 400 600 800 1000 1200</p> <p>Wavelength (nm)</p>                                                                                                                                                                                                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| <p><b>N-BK7 with VIS-NIR Coating</b><br/><b>Typical Transmission</b></p>  <p>100<br/>95<br/>90<br/>85<br/>80<br/>75<br/>70</p> <p>200 400 600 800 1000 1200 1400 1600</p> <p>Wavelength (nm)</p>    | <p>Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 0.25\% @ 880\text{nm}</math><br/><math>R_{avg} \leq 1.25\% @ 400 - 870\text{nm}</math><br/><math>R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p> |
| <p><b>N-BK7 with VIS 0° Coating</b><br/><b>Typical Transmission</b></p>  <p>100<br/>95<br/>90<br/>85<br/>80<br/>75<br/>70</p> <p>200 400 600 800 1000 1200</p> <p>Wavelength (nm)</p>              | <p>Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.4\% @ 425 - 675\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                                   |
| <p><b>N-BK7 with YAG-BBAR Coating</b><br/><b>Typical Transmission</b></p>  <p>100<br/>95<br/>90<br/>85<br/>80<br/>75<br/>70</p> <p>200 400 600 800 1000 1200 1400 1600</p> <p>Wavelength (nm)</p> | <p>Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 0.25\% @ 532\text{nm}</math><br/><math>R_{abs} \leq 0.25\% @ 1064\text{nm}</math><br/><math>R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>      |
| <p><b>N-BK7 with NIR I Coating</b><br/><b>Typical Transmission</b></p>  <p>100<br/>95<br/>90<br/>85<br/>80<br/>75<br/>70</p> <p>200 400 600 800 1000 1200 1400 1600</p> <p>Wavelength (nm)</p>    | <p>Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                                |
| <p><b>N-BK7 with NIR II Coating</b><br/><b>Typical Transmission</b></p>  <p>100<br/>95</p> <p>200 400 600 800 1000 1200 1400 1600</p> <p>Wavelength (nm)</p>                                      | <p>Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.</p>                                                                                                                                                                                                                                                                                                                                                                                                                          |



Coating Curves

Montures compatibles