

[Afficher tous les 23 produits de la même famille.](#)

InfiniTube FM-200 avec Composant en Ligne pour Objectifs +10X

See More by [Infinity Photo-Optical Company](#)



InfiniTube FM-200 (1X), #58-310



Stock **#58-311** **2 In Stock**

-

1

+

€1.675⁰⁰

AJOUTER AU PANIER

Prix sur Quantité	
Qté 1+	€1.675,00 prix unitaire
Need More?	Demande de Devis

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Caractéristiques du produit	
Fixed Magnification Lens	Type:
In-Line Illumination	Type d'Éclairage:
Propriétés optiques	

Objective Required

Taille maximale du capteur:

 $2/3'$

Monture:

C-Mount

RoHS 2015:

Conforme

Reach 224:

Conforme

Certificate of Conformance:

Visionner

- Directement sur caméras CCD à monture C et de formats 2/3" et moindre
- Focalisation interne

Les Systèmes InfiniTube™ FMest utilisé pour monter des objectifs conjugués à l'infini sur des caméras CCD, amenant des grossissements impossibles avec des objectifs ordinaires, tel qu'un grossissement 50X. Le système InfiniTube™ peut être configuré dans une large variété. Il peut être utilisé tout seul (InfiniTube™ #58-310 our #58-309) pour des applications où l'illumination est produite à partir d'une autre source telle qu'un backlight ou d'une illumination directionnelle. Le Système InfiniTube™ FMpeut aussi être configuré pour une illumination in-line avec des attachements. Le premier attachement in-line in-line (#58-313) fut conçu pour des objectifs ayant un grossissement 10X ou moindre et n'est pas conseillé pour des hautes puissances. Le second attachement in-line (#58-312) fut conçu pour fonctionner avec un efficacité supérieure lorsque utilisé avec des grossissements 10X ou plus, mais peut être utilisé avec tous grossissements. Tous les accessoires en ligne acceptent nos [Guides de Lumière à Fibre Optique](#) avec un diamètre de pointe de 0,312".

Note: **Système standard** pour capteurs 2/3" est toujours disponible.

The diagram illustrates various accessories for the Infinity™ FM-Series Main Bodies. At the top center is the #F9-686 DL Doubler Tube (2X). To its left is the #F7-788 C-Clamp w/ ¼"=20 Mounting Hole. Below the clamp are two infinity tube models: #F8-309 InfinityTube™ FM-100 and #F8-310 InfinityTube™ FM-200. To the right of the FM-200 is another #F7-788 C-Clamp w/ ¼"=20 Mounting Hole. Below the FM-100 is the #F8-313 InfinityTube™ In-Line Attachment Optimized for 2K to 10K Objectives. Below the FM-200 is the #F8-312 InfinityTube™ In-Line Attachment Optimized for 10K and higher Objectives. Between these two attachment points is the #F9-472 Collector II-HM. Below the FM-100 attachment point are three PL/FD Objective Adapter (M26) units labeled #F9-115 (PL/FD-195mm WD/0.25X), #F9-116 (PL/FD-295mm WD/0.165X), and #F9-117 (PL/FD-390mm WD/0.125X). Below the FM-200 attachment point are two Olympus US Objective Adapters (#F8-314) and one Nikon CF160 Objective Adapter (#F8-315). Below the adapter section are four objective lenses: #F55-402 (PL, 1.8mm WD/0.80X), #F55-403 (PL, 4.4mm WD/1.00X), #F55-404 (PL, 9.4mm WD/0.66X), and #F55-405 (PL, 9.4mm WD/0.50X). At the bottom center is the #F8-949 Mitutoyo/Achrovid™ Objective Adapter (M26) for 2X Objectives. On the far right is a Nikon CF160 Objective Adapter (#F8-315) connected to a Nikon CF160 Objective Lens (#F8-949).

Note:
The PL-Series Objectives are specifically designed to be used directly (no adapters required) with the InfinityTube™ FM-Series Main Bodies

All PL-Series Objectives are amplified by
2X (InfinityTube™ FM-100) or 4X (InfinityTube™ FM-200)
their engraved initial power ratings.

A DL 2X Tube can be used atop InfinityTube™ FM-Series
Main Bodies to further amplify magnification by a 2X factor.

System Includes		Stock No.
InfiniTube In-Line Assembly Unit		#58-311
Hitachi KP-D20B Camera		#55-837
15.1" Diagonal LCD Monitor (US version only)		#56-522
Y-C Cable (6 ft.)		#39-255
Mitutoyo/Achrovid™ Objective Adapter		#58-316
MI-150 Fiber Optic Illuminator		#55-718
Fiber Optic Light Guide (48" L)		#39-367
Fiber Optic Adapter		#38-944
Standard Boom Stand		#54-120
Rack & Pinion Mounting Plate		#54-123
C-Clamp with 1/4-20 Mounting Hole		#57-788