

[Afficher tous les 10 produits de la même famille.](#)

Teledyne Dalsa Xtium2-CXP PX8 CoaXPress Dual Frame Grabber

See More by [Teledyne DALSA](#)



Stock #91-738 **NOUVEAU** CONTACT

⊖ 1 ⊕ €1.140⁰⁰

AJOUTER AU PANIER

Prix sur Quantité

Qté 1+ €1.140,00 prix unitaire

Need More? [Demande de Devis](#)

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Caractéristiques du produit

OR-A8X0-XPX20 Numéro de Modèle:

Teledyne DALSA Fabricant:

Capteur

2GB Tampon d'Image:

Profondeur de Pixel:

Connectivité matérielle & interfaçage

CoaXPress **Interface:**

PCIe Gen3 x8 slot **Interface:**

2 Port (2 Cameras) **Ports:**

Conformité réglementaire

[Dispensé](#) **RoHS 2015:**

[Visionner](#) **Certificate of Conformance:**

Description produit

- High Data Throughput with Reliable, Low-Latency Image Transfer
- Minimizes CPU Usage and Improves Processing Times
- High Performance for Camera Link®, Camera Link® HS, GigE, and CoaXPress® Interface Standards

Teledyne DALSA Frame Grabbers provide high-performance image acquisition solutions for demanding machine vision and industrial imaging applications. Designed to support a wide range of camera interface standards and data rates, these frame grabbers deliver reliable, high-bandwidth image transfer with low latency. Advanced onboard processing capabilities and robust driver support simplify system integration while maximizing throughput. Teledyne DALSA Frame Grabbers are engineered for seamless compatibility with cameras from a wide range of manufacturers, enabling flexible deployment across diverse imaging platforms. With scalable configurations optimized for Camera Link, Camera Link HS, GigE, CoaXPress, and other leading interfaces, they provide an ideal solution for high-speed, high-resolution imaging environments. Frame Grabbers are specialized capture boards focused on capturing individual, high-resolution, or non-standard frames for machine vision applications.