


In order to provide more accurate inventory information, please select your shipping country.

Sélectionner votre Pays/Région: European Union ▼

SUBMIT



Coming® Varioptic® Variable Focus Liquid Lens Driver Board with Maxim MAX14574 Driver and I2C/DC Input



Stock #12-248 3-4 JOURS

⊖ 1 ⊕

€250,00

AJOUTER AU PANIER

Qté 1+

€250,00

Prix sur Quantité

[Demande de Devis](#)

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement



Dimensions (mm):
23 x 18 x 8

Remarque:
This board includes a MAX 14574 Maxim driver and

various FPC connectors (4 pin and 6 pin). It has a 4 pin JST connector for DC power supply and for I²C communication. It has been designed for fast driving of the adjustable lens directly from a microcontroller, an FPGA, a DSP, etc. A cabled JST connector is supplied with the board.

When used with an A-39Nx lens, the jumper in ST2 must be removed to ensure optimal performance and product lifetime. Watch this [video](#), or view the Technical Information tab, for more information

Conformité réglementaire

RoHS 2015: Conforme
Reach 224: Conforme
Certificate of Conformance: Visionner

