






**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER



|                          | VALUE                                   |
|--------------------------|---|
| CENTER WAVELENGTH (nm)   | 780nm                                   |
| FULL WIDTH HALF MAX (nm) | 10nm                                    |
| MINIMUM TRANSMISSION     | ≥85                                     |
| BLOCKING                 | 200 - 1200                              |
| SURFACE QUALITY          | 80-50                                   |
| CONSTRUCTION             | MOUNTED IN BLACK ANODIZED ALUMINUM RING |
| COATING TYPE             | HARD COATED                             |

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

|                        |    |        |   |              |
|------------------------|----|--------|---|--------------|
| THIRD ANGLE PROJECTION |    | TITLE  | OD4, Ø25mm, 780nm x 10nm, HC, BP FILTER |              |
| ALL DIMS IN            | mm | DWG NO | 65178                                   | SHEET 1 OF 1 |