

NOTES:

- 1. SUBSTRATE: FUSED SILICA
- 2. RoHS: COMPLIANT
- 3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 5 ARCMIN
- COATING (APPLY ACROSS COATING APERTURE) S1& S2: R(ABS) ≤1.0% FROM 350 - 450nm R(AVG) ≤1.5% FROM 250 - 700nm
- 5. FINE GRIND SURFACE



FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

SHAPE	S1 PLANO	s2 Plano			Edmund Optic	S [®]
SURFACE ACCURACY	1λ	1λ		TITLE	40mm DIA. UV - VIS COATED, 1λ FUSED SILICA WINDOW	
SURFACE QUALITY	60-40	60-40				
CLEAR APERTURE	Ø36.00	Ø36.00				CUEET
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN mm	DWG NO	84478	SHEET 1 OF 1