





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

| REV. A                     | VALUE        |
|----------------------------|--------------|
| CENTER WAVELENGTH (CWL)    | 450 ± 3 nm   |
| FULL WIDTH HALF MAX (FWHM) | 25 ± 3 nm    |
| MINIMUM TRANSMISSION       | ≥90          |
| BLOCKING                   | 200 - 1200nm |
| SURFACE QUALITY            | 80-50        |
| COATING TYPE               | HARD COATED  |
| DURABILITY                 | MIL-C-48497A |
| ENVIRONMENTAL              | MIL-STD-810F |

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**



THIRD ANGLE  
PROJECTION

TITLE

OD4,  $\varnothing 12.5\text{mm}$ , 450nm x 25nm, HD  
BANDPASS FILTER

ALL DIMS IN

mm

DWG NO

86641

SHEET  
1 OF 1