





+ 0.4861
x 0.5876
■ 0.6563



SURFACE: INA

DPA: 0.000 MM

SPOT DIAGRAM

47718
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 7.431
GD RADIUS : 19.486
SCALE BAR : 40


REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

CHROMATIC FOCAL SHIFT

47718
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 419.2216 μm
DIFFRACTION LIMITED RANGE: 58.776 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)




TRANSVERSE RAY FAN PLOT

47718
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 100.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



POLYCHROMATIC DIFFRACTION MTF

47718
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)