




NOTES:

1. SUBSTRATE:
Schott KG-1
2. COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: NONE



3. FINE GRIND SURFACE

4. WAVELENGTH RANGE: 300 - 2700 nm
5. DENSITY (g/cm³): 2.53
OPERATING TEMPERATURE (°C): 300 Maximum
REFLECTION FACTOR: 0.92
6. ROHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION		TITLE	12.5 x 12.5mm SCHOTT KG-1 Heat Absorbing Glass	
SHAPE	PLANO	PLANO	ALL DIMS IN	mm	DWG NO	45720	SHEET 1 OF 1
SURFACE QUALITY	60-40	60-40					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					