





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**




BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	1480 ± 2nm
FULL WIDTH HALF MAX (FWHM)	14 ± 2nm
MINIMUM TRANSMISSION	45%
BLOCKING	200 - 3500nm
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED RING
COATING TYPE	TRADITIONAL COATED

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

THIRD ANGLE  
PROJECTION



TITLE

Ø25mm, 1480nm x 14nm, BANDPASS FILTER

ALL DIMS IN

mm

DWG NO

47042

SHEET  
1 OF 1