




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



| REV. A                  | VALUE                       |
|-------------------------|-----------------------------|
| POLARIZATION EFFICIENCY | 95%                         |
| TRANSMISSION            | SINGLE: 30%; CROSSED: 0.15% |

|                                                                                                              |    |        |                                                       |                 |
|--------------------------------------------------------------------------------------------------------------|----|--------|-------------------------------------------------------|-----------------|
| THIRD ANGLE PROJECTION  |    | TITLE  | M22.5 x 0.5 MOUNTED LINEAR GLASS<br>POLARIZING FILTER |                 |
| ALL DIMS IN                                                                                                  | mm | DWG NO | 58649                                                 | SHEET<br>1 OF 1 |