





NOTES:

- 1. SUBSTRATE:
ND Filter Glass
- 2. OPTICAL DENSITY: 0.6
- 3. COATING SPECIFICATION:
AR Coating: MgF2
R(AVG) ≤1.75% @ 400 - 700nm
- 4. TRANSMISSION (%): 25
- 5. FILTER THREAD: M25.5 x 0.5

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING




SECTION A-A



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	THIRD ANGLE PROJECTION 				TITLE	FILTER ND MTD 0.6OD 25.5X0.5	
SHAPE	PLANO	PLANO	ALL DIMS IN	mm	DWG NO	59168		SHEET	1 OF 1
SURFACE QUALITY	80-50	80-50							