


NOTES:


- 1. SUBSTRATE:
FLOAT GLASS
- 2. COATING (APPLY ACROSS COATING APERTURE):
S1: INCONEL
S2: NONE

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



3. FINE GRIND SURFACE

- 4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS
APPLY ACROSS CLEAR APERTURE
- 5. ROHS COMPLIANT



T
λ
NEUTRAL DENSITY FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

	S1	S2				
SHAPE	PLANO	PLANO				
SURFACE QUALITY	80-50	80-50				
BLOCKING WAVELENGTH	400 - 700	400 - 700				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				
			THIRD ANGLE PROJECTION		TITLE	OD 0.4, Ø12.5mm REFLECTIVE ND FILTER
			ALL DIMS IN	mm	DWG NO	64128
						SHEET 1 OF 1