





**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

| REV. A                              | VALUE                |
|-------------------------------------|----------------------|
| SHAPE                               | PLANO                |
| SPECTRAL TRANSMITTANCE $\tau_p(\%)$ | 99                   |
| PASSBAND LIMIT $\lambda_p$ (nm)     | 470                  |
| CUT-OFF POSITION $\lambda_c$ (nm)   | 320±6                |
| STOPBAND LIMIT $\lambda_s$ (nm)     | 280                  |
| WAVELENGTH                          | UV                   |
| BEVEL                               | PROTECTIVE AS NEEDED |

 **Edmund Optics®**



ALL DIMS IN

mm

TITLE

Ø50mm, SCHOTT N-WG-320 LONGPASS FILTER

DWG NO

66074

SHEET  
1 OF 1