





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**




BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	514.5 ± 2nm
FULL WIDTH HALF MAX (FWHM)	3 ± 2nm
MINIMUM TRANSMISSION	35%
BLOCKING	200 - 1200nm
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED RING
COATING TYPE	TRADITIONAL COATED

Edmund Optics®

THIRD ANGLE
PROJECTION



TITLE

Ø12.5mm, 514.5nm x 3nm, BANDPASS FILTER

ALL DIMS IN

mm

DWG NO

66601

SHEET
1 OF 1