





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CUT-ON WAVELENGTH	500nm
TRANSMISSION WAVELENGTH	520 - 2000nm
REJECTION WAVELENGTH	200 - 480nm
TRANSMISSION	>85
SURFACE QUALITY	40-20
COATING TYPE	TRADITIONAL COATED

**Edmund Optics®**



THIRD ANGLE  
PROJECTION

TITLE

M25.5 x 0.5, 500nm MOUNTED LONGPASS  
FILTER

ALL DIMS IN

mm

DWG NO

66671

SHEET  
1 OF 1