





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CUT-ON WAVELENGTH	400nm
TRANSMISSION WAVELENGTH	420 - 2000nm
REJECTION WAVELENGTH	200 - 375nm
TRANSMISSION	>85
SURFACE QUALITY	40-20
COATING TYPE	TRADITIONAL COATED

Edmund Optics®



ALL DIMS IN

mm

TITLE

M30.5 x 0.5, 400nm MOUNTED LONGPASS
FILTER

DWG NO

66684

SHEET
1 OF 1