





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

REV A	VALUE
CENTER WAVELENGTH (CWL)	355 ± 2nm
FULL WIDTH HALF MAX (FWHM)	2.5± 2nm
MINIMUM TRANSMISSION	≥80 %
BLOCKING	326.6 - 349.7 & 360.3 - 390.5
SURFACE QUALITY	60-40
CONSTRUCTION	MOUNTED IN BLACK ANODIZED ALUMINUM RING
COATING TYPE	HARD COATED
DURABILITY	DURABILITY: MIL-C-48497A SECT. 3.4.1
ENVIRONMENTAL	ENVIRONMENTAL: MIL-STD-810F SECT. 507.4

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**



THIRD ANGLE  
PROJECTION

ALL DIMS IN

mm

TITLE

OD6, Ø12.5mm, 355 nm CWL, 1.3 nm  
BANDWIDTH, LASER LINE BANDPASS FILTER

DWG NO

68927

SHEET  
1 OF 1