




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

REV A	VALUE
CENTER WAVELENGTH (CWL)	488 $\pm$ 2nm
FULL WIDTH HALF MAX (FWHM)	3.4 $\pm$ 2nm
MINIMUM TRANSMISSION	≥ 90 %
BLOCKING	449 - 480.7 & 495.3 - 536.8
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED
DURABILITY	DURABILITY: MIL-C-48497A SECT. 3.4.1
ENVIRONMENTAL	ENVIRONMENTAL: MIL-STD-810F SECT. 507.4

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]



THIRD ANGLE
PROJECTION

ALL DIMS IN

mm

TITLE

OD6, Ø25mm, 488 nm CWL, 1.9 nm
BANDWIDTH, LASER LINE BANDPASS FILTER

DWG NO

68967

SHEET
1 OF 1