






**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



	VALUE
OPTICAL DENSITY	≥3.0
CENTER WAVELENGTH (CWL)	600 ±15 nm
FULL WIDTH HALF MAX (FWHM)	80 ±25 nm
MINIMUM TRANSMISSION	≥60 %
BLOCKING	200 - 1200nm
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED RING
COATING TYPE	TRADITIONAL COATED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 		TITLE	Ø25mm, 600nm x 80nm, MOUNTED BANDPASS FILTER	
ALL DIMS IN	mm	DWG NO	65745	SHEET 1 OF 1