





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	514.5nm
FULL WIDTH HALF MAX (FWHM)	3 ±1.0nm
MINIMUM TRANSMISSION	>80%
BLOCKING WAVELENGTH RANGE	400 - 509 & 520 - 700nm
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED



ALL DIMS IN

mm

EO® **Edmund Optics®**

TITLE

Ø12.5mm, 514.5nm CWL, 3nm FWHM, HARD
COATED LASER CLEAN-UP FILTER

DWG NO

68842

SHEET
1 OF 1