





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	980nm
FULL WIDTH HALF MAX (FWHM)	4 ±1.5nm
MINIMUM TRANSMISSION	>80%
BLOCKING WAVELENGTH RANGE	850 - 970 & 990 - 1300nm
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED



ALL DIMS IN

mm

EO® **Edmund Optics®**

TITLE

Ø12.5mm, 980nm CWL, 4nm FWHM, HARD
COATED LASER CLEAN-UP FILTER

DWG NO

68857

SHEET
1 OF 1